



Model (Standard Receiver)	SA360-DRWC SA361-DRW SA362-DRW	SA261-DRW SA262-DRW
Device Configurations		
Battery size 60-DRWC	Rechargeable Lithium-Ion	
Battery size 61-DRW	312 Zinc-Air	
Battery size 62-DRW	13 Zinc-Air	
Receiver Options	LP, MP, HP, UP	
Control Options	Push button (61-DRW and 60-DRWC), Multi-Function button (62), Telecoil (62)	
IP Classification	IP68	
Audiological Features		
Channels	12	10
Autoscope Adaptive Directionality (w/Adjustable Directional Mix)	●	-
Adjustable Directional Mix	●	-
Synchronized Soft Switching	●	●
Streaming Bass Boost	1 Setting	1 Setting
Fixed Directionality	●	●
Noise Tracker II	1 Setting	1 Setting
Wind Guard	1 Setting	1 Setting
Impulse Noise Reduction	1 Setting	-
Expansion	1 Setting	1 Setting
Sound Shaper	●	●
DFS Ultra III (w/Music Mode)*	●	●
Synchronized Acceptance Manager	●	●
Tinnitus Sound Generator	●	●
Functional Features		
Ear-to-Ear Communication	●	●
Bluetooth® Auracast™	●	●
Direct audio streaming (compatible iOS** and Android™ devices)	●	●
TV-Streamer+, Multi-Mic+ and Remote Control	●	●
ReSound Smart 3D™ app	●	●
Remote Fine Tuning and Updates		
ReSound Assist	●	●
ReSound Assist Live	●	●
Remote Firmware Updates	●	●
Fitting Features		
Fitting Software ReSound Smart Fit™ 2.1 or higher	●	●
Fully Flexible Programs	4	4
Datalogging	●	●
Wireless fitting with Noahlink Wireless	●	●
Automatic Receiver Detection	●	●

* Music Mode only available in Savi 4.

** MFi supports hands-free calls for iPhone 11 or later, iPad Pro 12.9-inch (5th generation), iPad Pro 11-inch (3rd generation), iPad Air (4th generation), iPad mini (6th generation) or later, with software updates iOS 15.3 and iPadOS 15.3 or later



Desktop charger
Charging form factor (CFF) 9



Premium charger
Charging form factor (CFF) 9



© 2024 GN Hearing A/S. All rights reserved. ReSound is a trademark of GN Hearing A/S. Apple, the Apple logo, iPhone and iPad are trademarks of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google LLC. The Bluetooth word mark and logos are registered trademarks owned by Bluetooth SIG, Inc.

402937011US CA VA-25.01-Rev.B

Manufacturer according to FDA:

Hearing aids
GN ReSound North America
8001 E Bloomington Freeway
Bloomington, MN 55420
USA
1-800-248-4327
pro.resound.com

ReSound Government Services
8001 E Bloomington Freeway
Bloomington, MN 55420
USA
1-800-392-9932
gs.resound.com

Manufacturer according to Health Canada:

Hearing aids
ReSound Canada
2 East Beaver Creek Road, Building 3
Richmond Hill, ON L4B 2N3
Canada
1-888-737-6863
resound.com

Manufacturer according to Health Canada:

Hearing aid charger
GN Hearing A/S
Lautrupbjerg 7
DK-2750 Ballerup
Denmark

Technical Specifications

		LP	MP	
		ANSI S3.22-2014 IEC 60118-0:2015 JIS C 5512: 2015 2cc coupler	ANSI S3.22-2014 IEC 60118-0:2015 JIS C 5512: 2015 2cc coupler	
Reference test gain (60 dB SPL input)	HFA	31	36	dB
Full-on gain (50 dB SPL input)	Max. HFA	56 50	60 55	dB
Maximum output (90 dB SPL input)	Max. HFA	113 109	115 113	dB SPL
Total harmonic distortion	500 Hz	0.6	0.7	%
	800 Hz	0.8	0.9	
	1600 Hz	1.4	1.3	
Telecoil sensitivity (1 mA/m input)*	Max.	87	90	dB SPL
HFA - SPLIV @ 31.6 mA/m (ANSI)	HFA	92	97	
Full-on telecoil sensitivity @ 1mA/m	HFA	81	86	
Equivalent input noise, w/o Noise reduction		22	20	dB SPL
1/3 Octave Equivalent input noise, w/o Noise reduction	1600 Hz	8	9	dB SPL
Frequency range		<200 - >8000	<200 - >8000	Hz
Battery Lifetime (Battery type Rechargeable)**		30 (max) 24 (typ)	30 (max) 24 (typ)	Hours
Current Drain (Quiescent / Operating) (Model 61-DRW, 62-DRW)		0.81 / 1.03	0.81 / 0.92	mA



* Telecoil is only for the Sx62-DRW models.
** Expected operating time of the rechargeable battery depends on active features, the use of wireless accessories, hearing loss, battery age and sound environment.
Maximum number includes no streaming; typical number includes several hours of streaming.

Technical Specifications



		HP	UP	
		ANSI S3.22-2014 IEC 60118-0:2015 JIS C 5512: 2015 2cc coupler	ANSI S3.22-2014 IEC 60118-0:2015 JIS C 5512: 2015 2cc coupler	
Reference test gain (60 dB SPL input)	HFA	41	46	dB
Full-on gain (50 dB SPL input)	Max. HFA	60 54	71 65	dB
Maximum output (90 dB SPL input)	Max. HFA	120 118	129 123	dB SPL
Total harmonic distortion	500 Hz	0.5	0.5	%
	800 Hz	0.8	0.4	
	1600 Hz	0.8	0.1	
Telecoil sensitivity (1 mA/m input)*	Max.	92	102	dB SPL
HFA - SPLIV @ 31.6 mA/m (ANSI)	HFA	103	106	
Full-on telecoil sensitivity @ 1mA/m	HFA	86	95	
Equivalent input noise, w/o Noise reduction		21	20	dB SPL
1/3 Octave Equivalent input noise, w/o Noise reduction	1600 Hz	9	8	dB SPL
Frequency range		<200 - 6590	<200 - 4650	Hz
Battery Lifetime (Battery type Rechargeable)**		30 (max) 24 (typ)	30 (max) 24 (typ)	Hours
Current Drain (Quiescent / Operating) (Model 61-DRW, 62-DRW)		0.81 / 0.94	0.81 / 0.87	mA

* Telecoil is only for the Sx62-DRW models.
** Expected operating time of the rechargeable battery depends on active features, the use of wireless accessories, hearing loss, battery age and sound environment.
Maximum number includes no streaming; typical number includes several hours of streaming.

Patents pending.





■ LP
■ MP





■ LP
■ MP

Patents pending.



■ HP
■ UP



■ HP
■ UP

All specifications are subject to change without notice.

All specifications are subject to change without notice.